3)	SUSUSUSUSUSUSUSUSUSUSUS	),
@		9
		S
XY		5)2
3		8
613 613		5/2
(F)	0-5-1-104-TE 0- 0411-5-14-10N	(3)
	CERTIFICATE OF CALIBRATION	
(K)	THIS IS TO CERTIFY THAT THE SHIMPO INSTRUMENT IDENTIFIED	(93)
3	BELOW HAS BEEN TESTED AT OUR FACTORY IN ACCORDANCE WITH APPROVED SHIMPO PROCEDURES. THE STANDARDS USED IN THE	8
613	CALIBRATION OF THIS UNIT ARE PERIODICALLY INSPECTED AND ARE TRACEABLE TO THE JAPAN NATIONAL RESEARCH LABORATORY OF	5)2
(3)	METROLOGY.	(3)
8	MODEL: FGV-20XY SERIAL NO	5/3
R	DATA CERTIFIED: $02/15/2008$ CAPACITY: $10 \text{ kg} \times 0.01 \text{ kg}$ ACCURACY: $\pm 0.2\%$ OF FULL SCALE $\pm 1/2$ LEAST SIGNIFICANT COUNT	(93)
		3
65	EQUIPMENT MODEL: DIGITAL MULTI METER 756202 DATA CALIBRATED: 04/13/2006	3/
	CALIBRATION DUE: 04/12/2008 OFFICIAL INSPECTION: SENSHIN ELECTRIC CO.,LTD.	8
(4)		(9)
	WEIGHTS USED: A-34 4000g, A-35 4000g, B-5 200g, B-6 400g, B-7 500g, B-61 400g, B-71 500g,	5.
	B-72 500g, B-73 500g, B-74 500g, B-75 500g, B-76 500g, B-77 500g DATA CALIBRATED: 04/02/2007	(J.)
6/5	CALIBRATION DUE: 04/01/2009	5/2
	OFFICIAL INSPECTION: EACH WEIGHT IS CALIBRATED BY ELECTRONIC BALANCE PM-6100.AND MP-300	3
(6)		(9)
		2
	CALIBRATED by	(J.)
665	手桥	2/3
		3
(6)		(3)
- ( )	PARARARA NININININININININININININININININININI	